

# YOUR BRAND

Your Tagline here - custom  
or choose from list




ANY  
TEXT HERE

# YOUR BRAND

Your Company  
Logo Here


# YOUR BRAND

**A Great General Purpose Progressive**  
The YOUR BRAND aspheric multi-design optimizes the reading area even in higher additions, with a wide intermediate and clear distance area for greater patient satisfaction.



Standard Corridor

**Fashionable and Functional**  
YOUR BRAND Short Progressive lenses have a wider channel for full use of the intermediate and an open distance area too, for maximum quality of vision.



Short Corridor

## Standard Availability

	CR39	Polycarbonate	CR39 Polarized	Photochromic SunSensors 1.56
Diameter	75mm Decentered 2.5mm	70/76mm Decentered 2.5mm	75mm Decentered 2.5mm	70/75mm Decentered 2.5mm
Base Curves	1.50, 3.25, 5.25, 7.25	0.75, 2.75, 4.75, 6.75, 7.75	1.50, 3.25, 5.25, 7.25	2.00, 4.25, 5.75 (75); 7.75 (70)
Additions	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps
Power Range	+6.50 to -7.25 sph, cyl to -4.00	+8.00 to -10.00 sph, cyl to -4.00	+6.50 to -8.00 sph, cyl to -4.00	+7.00 to -8.00 sph, cyl to -4.00
Fitting Height	18mm	18mm	18mm	18mm
Colors	Clear	Clear	Grey & Brown	Grey & Brown
Material Refractive Index	1.498	1.586	1.498	1.556

## Short Availability

	CR39	Polycarbonate	Photochromic SunSensors 1.56
Diameter	70/75mm Decentered 2.5mm	70/76mm Decentered 2.5mm	70/75mm Decentered 2.5mm
Base Curves	2.00, 4.25, 5.75 (75); 7.75 (70)	2.75, 4.75, 6.75 (76); 7.75 (70)	2.00, 4.25, 5.75 (75); 7.75 (70)
Additions	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps
Power Range	+7.00 to -8.00 sph, cyl to -4.00	+8.00 to -7.00 sph, cyl to -4.00	+7.00 to -7.00 sph, cyl to -4.00
Fitting Height	16mm	16mm	16mm
Colors	Clear	Clear	Grey & Brown
Material Refractive Index	1.498	1.586	1.556

Address  
Website  
Other contact info

Your Company  
Logo Here