

PROGRESSIVES

All Purpose and Short Corridor Progressives

Polycore All Purpose and Short Corridor Progressives are easy to wear and fashionable, with a wide variety of options to fit most any wearer.

Patient Satisfaction

Wearers adapt quickly to both of these aspheric soft-design progressives, and more flattering front curves assure a great look every time.



Extended Availability

Polycore progressives are available in a broad prescription range, with higher add-power options, and in a wide variety of lens materials.

Get What You Asked For

All minimum fitting heights are specified at 100% of the add power.

Polycore


Simplifying the Business of Sight

ALL PURPOSE F

	Hard Resin	Polycarbonate	Hard Resin Polarized	Photochromic SunSensors
Diameter	75mm Decentered 2.5mm	70/76mm Decentered 2.5mm	75mm Decentered 2.5mm	70/75mm Decentered 2.5mm
Base Curves	1.50, 3.25, 5.25, 7.25	0.75, 2.75, 4.75, 6.75, 7.75	1.50, 3.25, 5.25, 7.25	2.00, 4.25, 5.75, 7.75
Additions	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps
Power Range	+6.50 to -7.25 sph, cyl to -4.00	+8.00 to -10.00 sph, cyl to -4.00	+6.50 to -8.00 sph, cyl to -4.00	+7.00 to -10.00 sph, cyl to -4.00
Fitting Height	18mm	18mm	18mm	18mm
Colors	Clear	Clear	Grey & Brown	Grey & Brown
Material Refractive Index	1.498	1.586	1.498	1.556

A Great General Purpose Progressive

The Polycore All Purpose Progressive aspheric multi-design optimizes the reading area even in higher additions, with a wide intermediate and clear distance area for greater patient satisfaction.




SHORT CORRIDOR M

	Hard Resin	Polycarbonate	Photochromic SunSensors
Diameter	70/75mm Decentered 2.5mm	70/76mm Decentered 2.5mm	70/75mm Decentered 2.5mm
Base Curves	2.00, 4.25, 5.75 (75); 7.75 (70)	2.75, 4.75, 6.75 (76); 7.75 (70)	2.00, 4.25, 5.75 (75); 7.75 (70)
Additions	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps	1.00D to 3.50D in 0.25D steps
Power Range	+7.00 to -8.00 sph, cyl to -4.00	+8.00 to -7.00 sph, cyl to -4.00	+7.00 to -7.00 sph, cyl to -4.00
Fitting Height	16mm	16mm	16mm
Colors	Clear	Clear	Grey & Brown
Material Refractive Index	1.498	1.586	1.556

Fashionable and Functional

Polycore Short Corridor Progressive lenses have a wider channel for full use of the intermediate and an open distance area too, for maximum quality of vision.



At Polycore, we aim to reduce the complexity and confusion prevalent in our industry by simplifying the business of sight. Regardless of our technical sophistication or engineering innovation, you will experience the solid value in our products and in the ease of doing business with us.

Contact your local sales representative or Polycore USA for more details

polycore-usa.com

1-888-645-7788

Fax (775) 850-2060

895 East Patriot Blvd., Suite 110, Reno, NV 89511

Polycore

Simplifying the Business of Sight

**Our Products. Our People.
Experience the Polycore difference.**