

Vision Correction

Product Availability Varies Worldwide

Style	Diameter	Treatment	Power Range	Color
-------	----------	-----------	-------------	-------

Index 1.71

SFSV	65/70/75mm	Uncoated <b>NEW!</b>	Base curves: 0.25,1.50, 2.25, 3.00,4.50,5.25,6.00,7.00,7.75,8.75,11.00	Clear
------	------------	----------------------	------------------------------------------------------------------------	-------

Plastic 1.498

FSV	60mm	Hard Coated	+0.25D to +6.00 sph on -2.50 cyl	Clear
FSV	65mm	Uncoated, Hard Coated AR Coated, Super AR Coated	+0.25D to +6.00 sph on -2.50 cyl	Clear
FSV	70mm	Uncoated, Hard Coated AR Coated, Super AR Coated	0.00D to -6.00 sph on -2.50 cyl	Clear
FSV	70mm	Uncoated	+0.25D to +6.00 sph on -2.50 cyl	Clear
SFSV	70mm	Uncoated, Hard Coated	Base curves: 0.50,2.00,4.25,5.25,6.25,7.25,8.25,9.25,10.25	Clear
SFFT 28	70mm	Uncoated, Hard Coated	Base curves: 0.50,2.00,4.25,5.25,6.25,8.25,10.50 adds from 0.75 to 3.50 in 0.25 steps adds from 4.50 to 6.00 in 0.50 steps	Clear
SFFT 35	70mm	Uncoated	Base curves: 0.50,2.00,4.25,6.25,8.25,10.50 adds from 0.75 to 4.00 in 0.25 steps	Clear
SF TRI 7x28	70mm	Uncoated	Base curves: 2.00,4.25,6.25,8.25,10.50 adds from 1.00 to 4.00 in 0.25 steps adds from 4.50 to 6.00 in 0.50 steps	Clear
FUTURISE Progressive	75mm	Uncoated,Hard Coated	Base curves: 1.50,3.25,5.25,7.25 adds from 0.75 to 3.50	Clear
micr Progressive	70/75mm	Hard Coated	Base curves: 2.00,4.25,5.75,7.75 adds from 1.00 to 3.50	Clear

Polarized

Plano	78mm	Hard Coated	Plastic	6 base and 8 base	Grey,Brown,Green
SFSV	70/75mm	Hard Coated	Plastic	Decentered, Base curves: 0.50,2.00,4.25,5.25,6.25,8.25	Grey,Brown,Green
SFSV <b>NEW!</b>	70/75mm	Hard Coated	Plastic	Non-Decentered, Base curves: 0.50,2.00,4.25,5.25,6.25,8.25	Grey,Brown
SFFT 28	70mm	Hard Coated	Plastic	Base curves: 2.00,4.25,5.25,6.25,8.25 add from 0.75 to 3.50	Grey,Brown
FUTURISE Progressive	75mm	Hard Coated	Plastic	Base curves: 1.50,3.25,5.25,7.25 adds from 1.00 to 3.50	Grey,Brown

SunSensors (Photochromic 1.56)

FSV	65/70mm	Hard Coated,AR Coated	+4.00D to -6.00 sph on -2.00 cyl	Grey,Brown
SFSV	65/70mm	Hard Coated	Base curves 0.50 (65mm);2.00,4.25,5.75,7.75 (70mm)	Grey,Brown
SFFT 28	70mm	Hard Coated	Base curves: 2.00,4.25,5.25,6.25,8.50 add from 1.00 to 3.00	Grey,Brown
FUTURISE Progressive	70/75mm	Hard Coated	Base curves: 2.00,4.25,5.75 (75mm);7.75 (70mm) adds from 1.00 to 3.50	Grey,Brown
micr Progressive	70/75mm	Hard Coated	Base curves: 2.00,4.25,5.75,(75mm); 7.75 (70mm) adds from 1.00 to 3.50	Grey,Brown

Polycarbonate 1.586

FSV	70mm	Hard Coated,AR Coated, Super AR Coated	+4.00D to -6.00 sph on -2.00 cyl	Clear
FSV Asph	65mm	Hard Coated,AR Coated, Super AR Coated	+0.25D to +6.00D sph -2.00cyl	Clear
SFSV	76mm	Hard Coated	Base curves: 0.75,1.75,2.75,3.75,4.75,5.75,6.75,7.75,8.75	Clear
SFFT 28	76mm	Hard Coated	Base curves: 0.75,2.75,4.75,6.75,7.75 add from 1.00 to 3.50	Clear
FUTURISE Progressive	76mm	Hard Coated	Base curves: 0.75,2.75,4.75,6.75,7.75 adds from 1.00 to 3.50	Clear
micr Progressive	70/76mm	Hard Coated	Base curves: 2.75,4.75,6.75,7.75 adds from 1.00 to 3.50	Clear